

# CEREC SW 4.6: CEREC MC

| Motor set | Left         | Right                    | Combination                  |
|-----------|--------------|--------------------------|------------------------------|
| Set1      | Step Bur 12S | Cylinder Pointed Bur 12S | 1                            |
| Set1      | Step Bur 12  | Cylinder Pointed Bur 12S | 2                            |
| Set1      | Step Bur 20  | Cylinder Pointed Bur 20  | 3                            |
| Set1      | Shaper 25 RZ | Finisher 10              | 4 <sup>(1)</sup> Wet Milling |
| Set1      | Shaper 25    | Finisher 10              | 5 <sup>(2)</sup> Dry Milling |

<sup>(1)</sup> Only with grinding/milling units from the following serial number: CEREC MC 202001


<sup>(2)</sup> Requires grinding/milling unit with dry milling configuration and CEREC suction unit.

<sup>(3)</sup> USA/Japan

<sup>(4)</sup> Worldwide except Japan

<sup>(5)</sup> Japan

| Description              | Figure | Ref.      |
|--------------------------|--------|-----------|
| Step Bur 12S             | 1      | 62 40 167 |
| Step Bur 12              | 2      | 62 60 025 |
| Cylinder Pointed Bur 12S | 3      | 62 40 159 |
| Step Bur 20              | 4      | 62 59 597 |
| Cylinder Pointed Bur 20  | 5      | 62 59 589 |
| Shaper 25 RZ             | 6      | 64 33 440 |
| Finisher 10              | 7      | 62 99 387 |
| Shaper 25                | 8      | 62 99 395 |



| Manufacturer     | Material                             | Combination |
|------------------|--------------------------------------|-------------|
| Sirona           | CEREC Blocs C / CEREC Blocs          | 1 2         |
|                  | CEREC Blocs C PC / CEREC Blocs PC    | 1 2         |
|                  | CEREC Blocs C In                     | 1 2         |
|                  | CEREC Zirconia                       | 3 4 5       |
|                  | inCoris TZI C                        | 3 4 5       |
|                  | inCoris TZI                          | 3 4 5       |
| Dentsply Sirona  | CELTRA® Duo                          | 1 2         |
| 3M               | Lava™ Ultimate                       | 1 2         |
|                  | Paradigm™ MZ 100 <sup>(3)</sup>      | 1 2         |
| COLTENE          | BRILLIANT Crios                      | 1 2         |
| GC               | CERASMART™ <sup>(4)</sup>            | 1 2         |
|                  | CERASMART™ 270 <sup>(5)</sup>        | 1 2         |
|                  | CERASMART™ 300 <sup>(5)</sup>        | 1 2         |
|                  | Initial™ LRF                         | 1           |
| SHOFU            | BLOCK HC                             | 1 2         |
|                  | BLOCK HC (2L)                        | 1 2         |
| KURARAY NORITAKE | KATANA™ Zirconia Block (ST)          | 3 4 5       |
|                  | KATANA™ Zirconia Block (STML)        | 3 4 5       |
|                  | KATANA™ Avencia Block <sup>(5)</sup> | 1 2         |

| Manufacturer      | Material                 | Combination |
|-------------------|--------------------------|-------------|
| VITA              | VITABLOCS® MarkII        | 1 2         |
|                   | VITABLOCS® TriLuxe       | 1 2         |
|                   | VITABLOCS® TriLuxe forte | 1 2         |
|                   | VITABLOCS RealLife®      | 1 2         |
|                   | VITA ENAMIC®             | 1 2         |
|                   | VITA ENAMIC® multiColor  | 1 2         |
|                   | VITA SUPRINITY® PC       | 1 2         |
|                   | VITA SUPRINITY® FC       | 1 2         |
|                   | VITA YZ HT               | 3 4 5       |
| IVOCCLAR VIVADENT | IPS Empress® CAD         | 1 2         |
|                   | IPS Empress® CAD Multi   | 1 2         |
|                   | IPS e.max® CAD           | 1 2         |
|                   | IPS e.max® ZirCAD LT     | 3 4 5       |
|                   | Tetric® CAD              | 1 2         |